

# CENTER 380/382

## REFRIGERANT LEAK DETECTOR



### Features:

- *Microprocessor Control with advanced digital signal processing.*
- *Multi color visual display.*
- *High-Low leak sensitivity selector.(380)*
- *High-Med-Low sensitivity selector.(382)*
- *Low battery indication.*
- *Semiconductor gas sensor.*
- *Detection of R-134a, R-410A, R-407C, R22... Freon gas.*
- *Carrying case included.*
- *15.5" (40 CM) flexible stainless probe.*
- *Reference Leak source included.*
- *Ambient concentration reset.*
- *Long-life, DC brushless fan. (382)*
- *Variable intensity audible and visual alarms. (382)*

CE

# CENTER®

## FEATURES

Air Sucking System for faster response and higher sensitivity.(382)

Refrigerant Leakage Detector is the perfect tool for maintaining the air-condition or a cooling system with compressor and Refrigerant.

This unit used newly developed semi-conductor sensor which is extremely sensitive to variety of general used Refrigerant.

Microprocessor Control with advanced digital signal processing.

## SPECIFICATIONS

- Heated Semiconductor Gas Sensor.
- High-Low Leak Sensitivity Selector.(380)
- 3 Levels Of Sensitivity.(382)
- 7 LED Tri-colored Visual Leak Level Indicator.
- Variable Intensity Audible Alarm.
- Ambient Concentration Reset.
- 15.5"(40CM) Flexible Stainless Probe.
- Detection of R-134a, R-404A, R-410A, R-407C, R-22, R-502, R-600A...Refrigerants Gas.
- Sensitivity As Small 6gr/year(380); 3gr/year(382).
- Accordance With SAE J1627, CE Design.
- Low Battery Indication.
- Reference Leak Source Included.
- Hard Carrying case Included.
- Warm-up Time: 45 Seconds.(382)
- Operating Temperature: 0 to 40°C (32 to 104°F)
- Size: 21.7 x 6.6 x 5.6 cm
- Weight: 400g(with batteries)
- Power Source: 4 AA Size Alkaline Batteries.
- Battery Life: Appro. 40hrs(380)
- AC Adapter: @3.3V 0.5A(382)



DC 5V Jack(382)

\* The specifications and other information in this catalogue are subject to change without prior notice.

**CENTER**<sup>®</sup>  
**CENTER TECHNOLOGY CORP.**

4/F., NO.415, Jung-Jeng Rd., 23868 Shu-Lin, Taipei, Taiwan  
TEL: 886-2-26763926 E-Mail: center@centertek.com  
FAX: 886-2-26763925 http: //www.centertek.com

Distributed by: